

Desktop Computer AC Power Cable, NEMA 5-15P to C13 - 10A, 125V, 18 AWG, 10 ft. (3.05 m), Black

MODEL NUMBER: P006-010



Computer power cable allows you to connect your PC, printer or monitor into a surge protector, PDU or UPS with a NEMA 5-15R outlet.

Features

Desktop Computer Power Cord Connects PCs, Printers, Monitors and Other Equipment This computer power supply cable is designed for home/office desktop computer applications. You can use it to connect a computer, monitor, printer, scanner or other device with a C14 power inlet to an AC wall outlet, surge protector, UPS system or PDU. The 10-ft. (3.05 m) length allows you great flexibility in placing equipment with respect to the power outlet.

Specifications

OVERVIEW	
UPC Code	037332164780
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	125
PHYSICAL	
Cable Jacket Color	Black
Cable Jacket Material	PVC
Plug Color	Black

Highlights

- Recommended for powering computers, printers and other home/office peripherals
- 10-ft. (3.05 m) length allows great flexibility in placing devices in relationship to AC outlet
- NEMA 5-15P to C13 extension cord is ideal replacement for worn-out or missing cable

Applications

- Connect devices like computers, printers and monitors to a PDU up to 10-ft. (3.05 m) away in your workstation
- Extend an existing power connection up to 10-ft. (3.05 m) to more easily place a device or reach a power source
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P006-010 NEMA 5-15P to C13 Computer Power Cable, 10-ft. (3.05 m), Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Power Cord Jacket Type	SJT
Cable Jacket Rating	SJT
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.82
Cable Length (ft.)	10
Cable Length (m)	3.048
Shipping Dimensions (hwd / cm)	25.40 x 18.03 x 0.25
Shipping Dimensions (hwd / in.)	10.00 x 7.10 x 0.10
Shipping Weight (kg)	0.33
Shipping Weight (lbs.)	0.72
ENVIRONMENTAL	
Operating Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Storage Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Operating Humidity Range	10 TO 65% RH
Storage Humidity Range	10 TO 65% RH
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C13
SPECIAL FEATURES	
High Voltage	No
Locking Plug	No
Angled Plug	No
STANDARDS & COMPLIANCE	
Certifications	UL/Cul
Approvals	UL/CSA
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>