

24-Port 1U Rack-Mount STP Shielded Cat6 /Cat5 Feedthrough Patch Panel, RJ45 Ethernet, TAA

MODEL NUMBER: N254-024-SH



Highlights

- Shielded Cat6 RJ45 Jacks on both sides of the panel
- Installs easily in 19" racks or wall-mounts
- Cable management bar keeps patch cables well-ordered
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- Qualified to IEEE 802.3bt Type 4 PoE for up to 100W of power delivery

Package Includes

- 24-Port Shielded Cat6 Feed-Through 1U Patch Panel
- Detachable Cable Management Bracket

Description

This 24-Port Shielded Cat6 Feed-Through Patch Panel provides patching without punching down bulk wire to the back of the panel. Fully meets or exceeds Cat6 specifications. Works with USOC, T568A and T568B wiring. 19-inch width mounts easily in 2-Post relay rack or wall-mount hinged rack. Detachable cable management bar keeps Ethernet cables neat and tidy on the back of the panel. Easy screw-down strain relief eliminates the need for cable ties. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Heavy duty 14ga steel construction
- Fully shielded RJ45 / RJ45 Coupler jacks
- Meets or exceeds Cat6 specifications
- Easy patching with Shielded Cat6 patch cable
- Includes cable management bar
- Rackmountable - 19"W x 1.75"H (1U)
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332171122
Product Type	Rackmount
Technology	Cat5/5e; Cat6
CONNECTIONS	
Number of Ports	24



Powering Business Worldwide

TRIPP LITE
SERIES

PoE Power Budget (Watts)	30
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	RJ45 (FEMALE)
PoE Type	Type 4 High-Power (100W, IEEE 802.3bt)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	2.80 x 19.70 x 4.60
Shipping Dimensions (hwd / cm)	7.11 x 50.04 x 11.68
Shipping Weight (lbs.)	2.50
Shipping Weight (kg)	1.13
Unit Dimensions (hwd / in.)	1.700 x 19.000 x 1.250
Panel Style	Feed-Through
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.