

MINIATURE COAX THREADED 40/240 SERIES, TNC BULKHEAD JACKS

BJ41 Shown

INSULATED BULKHEAD JACK
REAR MOUNT, SOLDER POT
50Ω **BJ41**
75Ω **UBJ41**
Mounting Hole: D3.147

BJ40 Shown

BULKHEAD JACK
SOLDER POT
50Ω **BJ40**
75Ω **UBJ40**
W/ SOLDER LUG
50Ω **BJ40SL**
75Ω **UBJ40SL**
Mounting Hole: D5.125

BJ46-1 Shown

INSULATED BULKHEAD JACK
REAR MOUNT, WRENCH CRIMP
50Ω **BJ46-**
75Ω **UBJ46-**
Mounting Hole: D2.187
GF-Ground filter version page 31.

BJ47 Shown

INSULATED BULKHEAD JACK
FRONT MOUNT, SOLDER POT
50Ω **BJ47**
75Ω **UBJ47**
Mounting Hole: D3.147

BJ246-001 Shown

INSULATED BULKHEAD JACK
REAR MOUNT, TOOL CRIMP
50Ω **BJ246-**
75Ω **UBJ246-**
Mounting Hole: D2.187
GF-Ground filter version pg 31.

BJ49-1 Shown

BULKHEAD CABLE JACK
WRENCH CRIMP
50Ω **BJ49-**
75Ω **UBJ49-**
Mounting Hole: D3.218 / D2.218 (Cable Groups 6, 6E, 51, 52)

MODEL NO.	LTR CODE	OHM	A DIM	B DIM	C DIM	D DIM	E DIM
CBBJR46	-	50	.046	.24	.090	.050	.0625
UCBBJR46	-	75	.029	.24	.090	.050	.0625
CBBJR46A	A	50	.046	.34	.090	.058	.070
UCBBJR46A	A	75	.029	.34	.090	.058	.070

CBBJR46 Shown

INSULATED CIRCUIT BOARD JACK
RIGHT ANGLE
"A" refers to tall versions
50Ω **CBBJR46**
75Ω **UCBBJR46**
50Ω **CBBJR46A**
75Ω **UCBBJR46A**
Mounting Hole: D3.156

BULKHEAD CABLE JACK
TOOL CRIMP
50Ω **BJ249-**
Mounting Hole: D3.218 / D2.218 (Cable Groups 6, 6E, 51, 52)

MODEL NO.	LTR CODE	OHM	A DIM	B DIM	C DIM	D DIM	E DIM
CBBJR49	-	50	.046	.24	.090	.050	.0625
UCBBJR49	-	75	.029	.24	.090	.050	.0625
CBBJR49A	A	50	.046	.34	.090	.058	.070
UCBBJR49A	A	75	.029	.34	.090	.058	.070

CBBJR49 Shown

CIRCUIT BOARD JACK
BULKHEAD MOUNT
RIGHT ANGLE
Add "A" for tall versions
50Ω **CBBJR49**
75Ω **UCBBJR49**
Mounting Hole: D3.230

△ - Refers to Cable Group Table, see pages 68-88. "D" mounting holes are on page 45.