

TABLE 1	
DASH NO	DESCRIPTION
-1	CAP (NO CHAIN)
-2	CAP WITH 2.5 INCH BRASS CHAIN
-3	CAP WITH 2.5 INCH NYLON CHAIN
-4	CAP WITH 3.0 INCH BRASS CHAIN
-5	CAP WITH 3.0 INCH NYLON CHAIN
-6	CAP WITH 6.0 INCH BRASS CHAIN
-7	CAP WITH 6.0 INCH NYLON CHAIN
-8	CAP WITH 4.0 INCH BRASS CHAIN
-9	CAP WITH 4.0 INCH NYLON CHAIN
-10	CAP WITH 10.0 INCH BRASS CHAIN
-11	CAP WITH 10.0 INCH NYLON CHAIN
-12	CAP WITH 2.5 INCH SST ROPE
-13	CAP WITH 3.0 INCH SST ROPE
-14	CAP WITH 6.0 INCH SST ROPE
-15	CAP WITH 4.0 INCH SST ROPE
-16	CAP WITH 7.0 INCH SST ROPE
-17	CAP WITH 4.5 INCH SST ROPE
-18	CAP WITH 12 INCH SST ROPE


TABLE 2	
MODEL NO	TYPE
RFI155	3-LUG
RFI155	
RFI155FL	4-LUG
RFI155FL	
RFI355 $\triangle$	THREADED
RFI355 $\triangle$	

TABLE 3					
DASH NO	"A" DIA	"B" DIA	"C" DIM	"D" DIM	
-02	.630	.750	1.066	.450	
-03	.505	.625	.941	.388	
-04	.439	.562	.878	.355	
-05	.380	.500	.816	.325	
-06	.317	.437	.753	.295	
-07	.281	.406	.722	.278	
-08	.610	.750	1.066	.450	
-09	.567	.687	1.003	.419	
-010	.192	.312	.628	.231	
-011	1.005	1.125	1.441	.638	
-008	.330	.450	.766	.300	


DATA CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO TROMPETER ELECTRONICS, INC. AND SHALL NOT BE DISCLOSED, COPIED OR USED FOR REPRODUCTION OR MANUFACTURE WITHOUT EXPRESS WRITTEN PERMISSION OF TROMPETER ELECTRONICS, INC.

REVISIONS		1-0151	SH 1
REV	DESCRIPTION	DATE	APPROVED
M	REVISED PER ECO 15018	4-10-03	<i>MM</i>


RED INDICATES ORIGINAL




-1 SHOWN
NO STAINLESS STEEL ROPE CHAIN OR MOUNTING LUG




-2 THRU -11 SHOWN
STANDARD CHAIN AND BASIC MOUNTING LUG



-12 THRU -18 SHOWN
STAINLESS STEEL ROPE AND BASIC MOUNTING LUG



-12-02 THRU -18-008 SHOWN
STAINLESS STEEL ROPE AND BULKHEAD JACK MOUNTING LUG



-2-02 THRU -11-008 SHOWN
STANDARD CHAIN AND BULKHEAD JACK MOUNTING LUG

2. EXAMPLE OF COMPLETE MODEL NO:
RFI3155S-2-03
- BASIC MODEL NO $\triangle$ BULKHEAD JACK MOUNTING LUG (OPTIONAL) (SEE TABLE 3)
- $\triangle$ CHAIN/ROPE MATL AND LENGTH (SEE TABLE 1)

1. MALE 3 & 4-LUG & THREADED STYLE SUBMINIATURE RFI DUST CAP WITH OR WITHOUT CHAIN OR JACKETED STAINLESS STEEL ROPE AND MOUNTING OPTION

$\triangle$ NOTE THAT CHAIN LENGTH FOR SST ROPE WITH MOUNTING LUG OPTION IS NOT MEASURED TO CENTER OF BULKHEAD MOUNTING LUG

$\triangle$ IF SAFETY WIRE REQUIRED ADD SUFFIX "S" TO MODEL NO. (i.e. RFI3155S)

INTERPRET DRAWING PER		TOL.: UNLESS SPECIFIED	
NO. STD-100	CONVERSIONS ARE IN INCHES	XX	.XXX ±.005
NO. INCLUDE FINISH	FINISHES	XXXX	ANGLES
UNLESS OTHERWISE SPECIFIED			
DRAWN: AAH	DATE: 4-9-03	MATERIAL:	
CHECKED: SS	DATE: 4/9/03	FINISH:	
QUALITY: JF	DATE: 4/10/03		
APPROVED: <i>MM</i>	DATE: 4/10/03		
CAD FILE NO: 1-0151M			



TITLE: RFI155/RFI155/
RFI155FL/RFI155FL/
RFI355/RFI355

SIZE	CAGE CODE	DRAWING NO.	REV.
B	14949	1-0151	M
SCALE	DATE	SHEET	
2/1	2-22-77	1C	

NEXT ASSY

DO NOT SCALE DIM