


RED INDICATES ORIGINAL


DASH NO	CABLES ACCOMMODATED	A DIM	B FLATS	C HEX	ASSEMBLE PER
-1	RG-58				
-U1	ESSEX 621-715				
-2	RG-59				
-U2					
-2A	BELDEN 8279				
-U2A					
-2B	W.E.CO. 730A				
-U2B					
-3					
-U3	RG-223	.906	.437	.437	TAI-101
-3A					
-U3A	RG-55				
-4	RG-122				
-U4	BELDEN 8218				
-5	RG-174				
-U5	RG-187				
-5A					
-U5A	RG-196				
-5B	HEWLETT-PACKARD 8120-1107				
-U5B					
-6	BELDEN 9231	.963	.500	.500	TAI-119
-6E	RG-5				
-U6E	RG-6				
-21	RG-303				
-U21					
-22	RG-180				
-U22					
-34	BELDEN 8228	.906	.437	.437	TAI-101
-36	275-3991 MICRODOT				
-U36	616-569 AMPEX				
-37					
-U37	610 RAYCHEM				
-41	RG-304				
-U41	BELDEN 9248/9284/9383				
-44	BRAND-REX B749				
-U44	GORE C06C032				
-51	88281 BELDEN	.963	.500	.500	TAI-119
-U51					
-52	89120 BELDEN				
-U52					
-53	89555 BELDEN	.906	.437	.437	TAI-101
-U53					
-63	734A.AT&T				
-U63					

FIG 1
- 1 SHOWN



INCH	MM
.005	0.13
.030	0.76
.096	2.44
.125	3.18
.437	11.10
.500	12.70
.562	14.27
.906	23.01
.963	24.46
1.846	46.89

FIG 2
- 1 SHOWN



△ IF BEND RELIEF SPRING REQUIRED, ADD SUFFIX "BR" TO MODEL NO. (SEE FIG 2) (NOT AVAILABLE WITH CABLE GROUPS -6, -U6, -6E, -U6E, -51, -U51, -52, -U52, -63 & -U63)

- MALE COAXIAL PUSH-ON PLUG BOTH 50 & 75 OHM VERSION (BNC STYLE)
- DASH NO DENOTES CABLE GROUP EXCEPT "U" PREFIX DENOTES 75 OHM VERSION
- FINISH: TFS-1A (NICKEL)
- ALL DIM ARE IN INCHES

DISK #	DATA CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO TROMPETER ELECTRONICS, INC. AND SHALL NOT BE DISCLOSED, COPIED OR USED FOR PROCUREMENT OR MANUFACTURE WITHOUT EXPRESS WRITTEN PERMISSION.	REV	EO	DESCRIPTION	1-0390	SH 1
C 5		6	8594	ADDED -63 CABLE GROUP-DWG NO WAS 1000-0390 & REDRAWN	DWN	DATE

QTY	DESCRIPTION	PART NUMBER	ITEM
TOL UNLESS SPECIFIED .XX ± .XXX ± .005 .XXXX ± ANGLES	TROMPETER ELECTRONICS, INC.	PL123/UPL123	
DWN	DJK 9/15/89	MATERIAL	CODE IDENT
CHK	1/11/81	14949	DRAWING NO.
ENGR	10/31/89	1-0390	REV
APPR	1/3/89	SCALE 2/1	DATE 7/6/76
12-06	NEXT ASSY		SHEET 1 OF 2