

Specification Sheet

Part Number: 151-00174



Edge Clip Cable Clamp, Panel Thickness .04" -.012 ", PA6HIR, Black, 250/pk

Article Number

151-00174

Type

EC39

Color

Black (BK)

Features & Benefits

HellermannTyton's edge clips are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place. These edge clips are an edge clip and tape bar combination, which can be secured to cables with cable ties or tape.

Quantity Per

bag

Product Description

HellermannTyton's edge clip and tape clip assembly is ideal for use in applications where holes are not acceptable. Edge clips are widely used for fixing and bundling cables and wires within in the automobile, harness making, panel building and electrical industries

Short Description	Edge Clip Cable Clamp, Panel Thickness .04" -.012 ", PA6HIR, Black, 250/pk
Global Part Name	EC39-PA6HIR-BK
Length L (Imperial)	4.6
Fixation Method	Edge Clips
Width W (Imperial)	5.2
Bundle Diameter Min (Imperial)	0.614
Bundle Diameter Min (Metric)	15.3
Bundle Diameter Max (Imperial)	0.63
Bundle Diameter Max (Metric)	15.9
Nominal Diameter (Imperial)	5/8
Nominal Diameter (Metric)	15.6
Panel Thickness Min(Imperial)	0.04
Panel Thickness Max(Imperial)	0.12
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	3.0

Material	Polyamide 6, high impact modified (PA6HIR)
Material Shortcut	PA6HIR
Flammability	UL 94 HB
Operating Temperature (Metric)	-40°F to +176°F (-40°C to +80°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	250
Package Quantity (Metric)	250
Customs Number	3926909987
Content Unit(BMEcat)	pcs.