

## P108-16-MOD

**Article Number:** 853-19201

**Modular Patch Panel 16 Port, 1U, Steel, Black, 1/box**



[Download spec sheet](#)

### Base Data

**Local Order Number** P108-16-MOD

**Type** P108-16-MOD

**Color** Black (BK)

**Features and Benefits**

- The modular design provides flexibility with the panel for customization of different applications including coax, voice, audio, video and fiber.
- Once the connectors are snapped into the panel, they are flush with the front of the plate providing an aesthetic look.

**Product Description** The modular patch panel is designed to accept HellermannTyton Category 6A, 6 and 5e UTP modular jacks and connectors, providing flexibility in multimedia installations. These modular panels can be mounted to any standard EIA 19" rack, cabinet or wall mount patch panel bracket. HellermannTyton pre-numbered modular patch panels are available in 12, 16, 24, 32 and 48 port configurations.

**Short Description** Modular Patch Panel 16 Port, 1U, Steel, Black, 1/box

### Product Dimensions

**Length L (Imperial)** 19.0 "

**Length L (Metric)** 482.6 mm

**Height in Units** 1U

**Height H (Imperial)** 1.75 "

**Height H (Metric)** 44.45 mm

### Logistics and Packaging

**Quantity Per** box

**Package Quantity** 1

**Package Quantity (Metric)** 1

**Carton Quantity** 5

### Material and Specifications

**Material** Steel (ST)

**Material Shortcut** ST