

## Specification Sheet


Part Number: 111-00718

ETFE cable ties provide excellent resistance to chemicals, radiation, high temperatures and UV exposure.

Inside serrations allows for strong grip on cables and wire bundles.

Head design provides high tensile strength with very low insertion force.

Bent tail ensures a quick and simple installation.



High-Temp Cable Tie, 15" Long, 50lb Tensile Strength, ETFE, Blue, 100/pkg

Article Number 111-00718

Type T50L

Color Blue (BU)

Quantity Per pack

**Product Description**

ETFE ties provide excellent protection against radiation, ultraviolet light, and a wide range of chemicals. They are also rated for low outgassing applications. HellermannTyton's ETFE ties come in a standard color of blue for easy identification. T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description	High-Temp Cable Tie, 15" Long, 50lb Tensile Strength, ETFE, Blue, 100/pkg
Global Part Name	T50L-E/TFE-BU
Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	15.0
Length L (Metric)	381.0
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.19
Width W (Metric)	4.7
Bundle Diameter Min (Imperial)	0.2
Bundle Diameter Min (Metric)	5.0
Bundle Diameter Max (Imperial)	4.13
Bundle Diameter Max (Metric)	105

Thickness T (Imperial)	0.06
Thickness T (Metric)	1.7
Cable Tie Head Length (Imperial)	0.28
Cable Tie Head Width (Imperial)	0.32
Material	Ethylenterafluoroethylene (E/TFE)
Material Shortcut	E/TFE
Flammability	UL 94 V-0
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-112°F to +338°F (-80°C to +170°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL   ANSI/UL 1565 UL   ANSI/UL 62275
UL Recognized (US)	Yes
Package Quantity (Imperial)	100

Package Quantity (Metric) 100

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)