

## Specification Sheet

Part Number: 111-95149

The 316 grade stainless steel offers excellent resistance to salt spray, corrosion, weather and chemicals.

Self-locking, ball bearing mechanism for quick and easy installation, either by hand or tensioning tool.

Fully enclosed head prevents debris from interfering with locking mechanism.

High tensile strength for maximum strength and safety in heavy duty applications.



Article Number 111-95149

Type MBT14XH

Color Metal (ML)

Quantity Per pack

Product Description HellermannTyton's Stainless Steel Ties are designed with a ball bearing locking mechanism to ensure high tensile strength and easy insertion when securing hoses, cables, pipes and more. Stainless steel ties can be used in virtually any indoor, outdoor or underground application. Grade 316 material is highly resistant to corrosion and widely used in marine environments where chemicals, salts, acids and temperature extremes may affect the bundling application.

Short Description	Stainless Steel Tie, 14.3" Long, 607lb Tensile Strength, SS316, Metal, 50/pkg
Global Part Name	MBT14XH-SS316L-ML
Minimum Tensile Strength (Imperial)	607
Minimum Tensile Strength (Metric)	2700
Length L (Imperial)	14.3
Length L (Metric)	362.0
Identification Plate Position	none
Releasable Closure	No
Tie Closure	ball bearing lock
Variant	Not Serrated
Width W (Imperial)	0.48
Width W (Metric)	12.3
Bundle Diameter Min (Imperial)	0.47
Bundle Diameter Min (Metric)	12.0
Bundle Diameter Max (Imperial)	4.02
Bundle Diameter Max (Metric)	102.0

Thickness T (Imperial)	0.01
Thickness T (Metric)	0.3
Cable Tie Head Length (Imperial)	0.55
Cable Tie Head Width (Imperial)	0.57
Material	Stainless Steel (SS316L)
Material Shortcut	SS316L
Flammability	Non-burning
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Operating Temperature	-112°F to +1000°F (-80°C to +538°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	DNV   IEC 62275 Bureau Veritas   IEC 60092 ABS   IEC 62275:2018 UL   csa-C22.2 no. 62275 UL 62275
UL Listed (US and Canada)	Yes

Package Quantity (Imperial) 50

Package Quantity (Metric) 50

Customs Number 7326908695

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)