

Specification Sheet

Part Number: 115-00046



Release feature allows maintenance or changeouts as needed.

Polyamide 6.6 cable ties deliver excellent resistance to chemicals and salts.

Inside serrations provide strong grip on cables and wire bundles.

Reliable bundle fastening plus low insertion force for ease of use.

Article Number 115-00046

Type RF140

Color Black (BK)

Quantity Per pack

Product Description Releasable Cable Ties feature an integrated release mechanism on the head, allowing for changeouts without destroying the cable tie. The head design ensures consistently high tensile strength, even after repeated use. Rounded tail glides into head with low insertion force.

Short Description Releasable Cable Tie, Release Lever, 5.5" Long, 50lb Tensile Strength, PA66, Black, 100/pkg

Global Part Name RF140-PA66-BK

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	5.5
Length L (Metric)	140.0
Fixation Method	Releasable Cable Tie
Identification Plate Position	none
Releasable Closure	Yes
Width W (Imperial)	0.29
Width W (Metric)	7.4
Bundle Diameter Min (Imperial)	0.1
Bundle Diameter Min (Metric)	2.5
Bundle Diameter Max (Imperial)	1.26
Bundle Diameter Max (Metric)	32.0
Thickness T (Metric)	1.2
Material	Polyamide 6.6 (PA66)

Material Shortcut	PA66
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL ANSI/UL 1565 UL ANSI/UL 62275
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)