

## Specification Sheet

Part Number: 132-00011



Unique two piece tie allows parallel entry and exit through the head for easy assembly.

High impact, heat stabilized material gives strength needed for trucking and heavy equipment applications.

Article Number 132-00011

Type BT105L

Color Black (BK)

Quantity Per pack

Product Description The button head tie is a two piece tie providing for parallel entry and exit through the head. The strap contains serrations on both sides, and has two opposed pawls recessed within a domed head. This design allows the strap to be directed clockwise or counter-clockwise prior to insertion into the head, enabling bi-directional looping.

Short Description Button Head Cable Tie, 15.0" Long, 4.3" Max Bundle Dia, 105lb, PA66HIRHSUV/PA66HS, Black, 50/pkg

Global Part Name BT105L-PA66HIRHSUV/PA66HS-BK

Minimum Tensile Strength (Imperial)	105
Minimum Tensile Strength (Metric)	467
Length L (Imperial)	15.0
Length L (Metric)	381.5
Fixation Method	Button Head
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Outside Serrated
Width W (Imperial)	0.22
Width W (Metric)	5.6
Bundle Diameter Min (Imperial)	0.25
Bundle Diameter Min (Metric)	6.4
Bundle Diameter Max (Imperial)	4.33
Bundle Diameter Max (Metric)	110.0
Mounting Hole Diameter D (Metric)	22.0 mm

Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV PA66HS
Material Cable Tie	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Head	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)