

Specification Sheet

Part Number: 148-00200

Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.

Edge Clip provides low insertion force and high extraction force ideal for assembly environments.

Cable tie is outside serrated to reduce bundle chafing.



1-Piece Cable Tie with Edge Clip, 8" Long, EC12, Panel Thickness 0.04 - 0.12", 50 lbs, PA66HS, Black, 500/bg

Article Number	148-00200
----------------	-----------

Type	T50SOSEC12E
------	-------------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	The cable tie and edge clip assembly is ideal for use where holes are not acceptable or where adhesives will fail due to temperature problems. Edge clips are widely used for fixing and bundling cables and wires within automotive, trucking, heavy equipment, solar panel, wind power, and white goods equipment manufacturing.
---------------------	--

Short Description	1-Piece Cable Tie with Edge Clip, 8" Long, EC12, Panel Thickness 0.04 - 0.12", 50 lbs, PA66HS, Black, 500/bg
-------------------	--

Global Part Name	T50SOSEC12E-PA66HS-BK
------------------	-----------------------

Minimum Tensile Strength (Imperial)	40
-------------------------------------	----

Minimum Tensile Strength (Metric)	180
-----------------------------------	-----

Length L (Imperial)	6.0
---------------------	-----

Length L (Metric)	160.0
-------------------	-------

Fixation Method	Edge Clip
-----------------	-----------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Outside Serrated
---------	------------------

Width W (Imperial)	0.18
--------------------	------

Width W (Metric)	4.6
------------------	-----

Bundle Diameter Min (Imperial)	0.04
--------------------------------	------

Bundle Diameter Min (Metric)	1.0
------------------------------	-----

Bundle Diameter Max (Imperial)	1.38
--------------------------------	------

Bundle Diameter Max (Metric)	35.0
------------------------------	------

Thickness T (Imperial)	0.05
Thickness T (Metric)	1.35
Height H (Imperial)	0.06
Height H (Metric)	1.35
Panel Thickness Min (Imperial)	0.04
Panel Thickness Max (Imperial)	0.12
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	3.0
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes

ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)