

Specification Sheet

Part Number: 151-02977



One base fits more surfaces – flat, curved and moderately angled – for versatile applications.

High-strength, weather-resistant adhesive offers excellent performance indoors and out.

4-way opening allows parallel or perpendicular cable routing options.

Flexible Cable Tie Mounting Base, 1.1 x 1.1", 0.21" Max Tie Width, PA66HS, White, 100/pkg

Article Number	151-02977
Type	FMB4APT-A
Color	White (WH)
Quantity Per	pack
Product Description	HellermannTyton FlexTack Adhesive Cable Tie Mounts deliver excellent mounting performance on flat, curved and moderately angled surfaces. Use in combination with 18- through 50-pound cable ties to provide stability when securing bundles. The adhesive on this mount is approved for use on low- to medium-energy surfaces in automotive applications, such as clear-coats and plastics; railway, aerospace and heavy equipment; and where drilling a hole is not possible or desirable. The 4-way saddle allows cable ties to be inserted parallel or perpendicular to the wire bundles.

Short Description	Flexible Cable Tie Mounting Base, 1.1 x 1.1", 0.21" Max Tie Width, PA66HS, White, 100/pkg
Global Part Name	FMB4APT-A-PA66HS-WH
Length L (Imperial)	1.1
Length L (Metric)	28.0
Fixation Method	Adhesive
Width W (Imperial)	1.1
Width W (Metric)	28.0
Height H (Imperial)	0.25
Height H (Metric)	6.3
Cable Tie Width Max (Imperial)	0.2
Cable Tie Width Max (Metric)	5.4
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Adhesive	Acrylate with base of acrylic foam

Flammability	UL 94 V-2 (excluding adhesive)
Halogen Free	Yes
Use Conditions	For Indoor Use Only
Adhesive Operating Temperature	-40°F to +194°F (-40°C to +90°C)
Operating Temperature	-40°F to +194°F (-40°C to +90°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com