

Specification Sheet

Part Number: 151-10914



2- or 4-way entry options for the Q Tie, offering flexibility and stability

Q Tie Mount with Adhesive, 0.79 x 0.79 x 0.17", 4 way entry for Q18 - Q30 ties, PA66, Black, 100/bg

Article Number 151-10914

Type QM20A

Color Black (BK)

Quantity Per pack

Product Description Q Mounts are designed to work exclusively with the Q Tie cable tie series. This mounting component is available with adhesive or can be secured with screws. The Q Mount allows either a 2- or 4-way entry for the Q Tie, providing a quick and simple insertion into the mount. Once in place, the Q Tie will not slip out, even in vertical mounting applications.

Short Description Q Tie Mount with Adhesive, 0.79 x 0.79 x 0.17", 4 way entry for Q18 - Q30 ties, PA66, Black, 100/bg

Global Part Name	QM20A-PA66-BK
Length L (Imperial)	0.79
Length L (Metric)	20.0
Fixation Method	Adhesive
Width W (Imperial)	0.79
Width W (Metric)	20.0
Height H (Imperial)	0.17
Height H (Metric)	3.7
Cable Tie Width Max (Imperial)	0.14
Cable Tie Width Max (Metric)	4.0
Mounting Hole Diameter D (Imperial)	0.12 "
Mounting Hole Diameter D (Metric)	3.1 mm
Mounting Hole Centers (Imperial)	0.53
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66

Adhesive	Synthetic rubber with base of polyethylene foam
Flammability	UL 94 V-2 (excluding adhesive)
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Adhesive Operating Temperature	-40°F to +140°F (-40°C to +60°C)
Operating Temperature	-40°F to +140°F (-40°C to +60°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)