

Specification Sheet

Part Number: 155-05400



Oval mount design pushes on easy by hand without the need for tools.

Design provides low insertion and high extraction force.

1-Piece 5.0mm Stud Mount Cable Tie with Oval Mounting Hole, 6.0" Long, 50lb Tensile Strength, PA66HS, Black, 500/pkg

Article Number 155-05400

Type T50SOSSB5-HIGH-E

Color Black (BK)

Quantity Per pack

Product Description The special oval shape provides for an approximate .20" (5.0 mm) lateral adjustment, allowing for any misalignment of the stud or incorrect positioning of the tie on the cables

Short Description 1-Piece 5.0mm Stud Mount Cable Tie with Oval Mounting Hole, 6.0" Long, 50lb Tensile Strength, PA66HS, Black, 500/pkg

Global Part Name T50SOSSB5-HIGH-E-PA66HS-BK

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	170
Length L (Imperial)	6.0
Length L (Metric)	160
Fixation Method	Stud Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Outside Serrated
Width W (Imperial)	0.19
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.04
Bundle Diameter Min (Metric)	1.0
Bundle Diameter Max (Imperial)	1.38
Bundle Diameter Max (Metric)	35.0
Thickness T (Imperial)	0.05

Thickness T (Metric)	1.35
Stud Length Max (Imperial)	0.63
Stud Length Max (Metric)	16.0
Stud Length Min (Metric)	11.0
Stud Diameter (Metric)	5.0 mm

Material Polyamide 6.6 heat stabilized (PA66HS)

Material Shortcut PA66HS

Flammability UL 94 V-2

UV Resistant (Yes/No) No

Use Conditions For Indoor and Outdoor Use

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 500

Package Quantity (Metric) 500

Customs Number

3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)