

Specification Sheet

Part Number: 155-46302



Oval mount design pushes on easy by hand without the need for tools.

Design provides low insertion and high extraction force.

1-Piece 6.0mm Stud Mount Cable Tie with Oval Mounting Hole, 6.0" Long, 50lb Tensile Strength, PA66HS, Black, 500/pkg

Article Number 155-46302

Type T50SOSSB6HE

Color Black (BK)

Quantity Per pack

Product Description Oval Shaped Stud Mount's special design allows for a .20" (5.5 mm) lateral adjustment, allowing for any misalignment of the stud or incorrect position of the tie on the cables. The mount allows it to be installed onto a weld stud without the use of any tools.

Short Description 1-Piece 6.0mm Stud Mount Cable Tie with Oval Mounting Hole, 6.0" Long, 50lb Tensile Strength, PA66HS, Black, 500/pkg

Global Part Name T50SOSSB6HE-PA66HS-BK

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	170
Length L (Imperial)	6.0
Length L (Metric)	160.0
Fixation Method	Stud Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Outside Serrated
Width W (Imperial)	0.19
Width W (Metric)	4.7
Bundle Diameter Min (Imperial)	0.04
Bundle Diameter Min (Metric)	1.0
Bundle Diameter Max (Imperial)	1.38
Bundle Diameter Max (Metric)	35.0
Thickness T (Imperial)	0.05

Thickness T (Metric)	1.35
Stud Length Min (Metric)	16.0
Stud Diameter (Metric)	6.0 mm
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)