

Specification Sheet

Part Number: 156-01296



Head allows for a 0.2" lateral adjustment on stud during installation

Quick and easy installation ideal for manufacturing environment

2-Piece Cable Tie with Oval Stud Mount, 8.0" Long, 50lb Tensile, With Thumb Bar, PA66HS/PA66HIRHSUV, Black, 2000/box

Article Number 156-01296

Type T50R0SBL6USET

Color Black (BK)

Quantity Per pack

Product Description Oval Shaped Stud Mount's special design allows for a 0.2" (5.5mm) lateral adjustment, allowing for any misalignment of the stud or incorrect position of the tie on the cables. The "soft push" mount allows it to be installed onto a weld stud without the use of any tools.

Short Description 2-Piece Cable Tie with Oval Stud Mount, 8.0" Long, 50lb Tensile, With Thumb Bar, PA66HS/PA66HIRHSUV, Black, 2000/box

Global Part Name T50R0SBL6USET-PA66HS/PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	8.0
Length L (Metric)	203.2
Fixation Method	Stud Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Bundle Diameter Min (Imperial)	0.16
Bundle Diameter Min (Metric)	4.0
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Height H (Imperial)	1.02
Height H (Metric)	25.0
Mounting Hole Diameter D (Metric)	M6 x 1
Stud Diameter (Metric)	M6

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) Polyamide 6.6 heat stabilized (PA66HS)
Foot Part Material	PA66HIRHSUV
Material Shortcut	PA66HS PA66HIRHSUV
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

