

Specification Sheet

Part Number: 156-01339



Bundle can rotate to any orientation, allowing routing in any direction regardless of mounting point.

Clip is reusable, making relocation or adjustments simple.

All-in-one bundling and mounting solution reduces costs.

1-Piece Cable Ties with Pipe Clip, 6.0" Long, Attaches to Diameter .59" - .71", PA66HS, Black, 500/pkg

Article Number	156-01339
Type	T50SVCOC15-18
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton’s 1-Piece Cable Tie with Pipe Clip secures cables to tubular frame rails. The cable tie bundles wires, cables or tubes, and the C-clip snaps onto the tubular frame rail. The clip can be removed from the mounting surface and reinstalled without additional fasteners.
Short Description	1-Piece Cable Ties with Pipe Clip, 6.0" Long, Attaches to Diameter .59" - .71", PA66HS, Black, 500/pkg
Global Part Name	T50SVCOC15-18-PA66HS/PA66HIRHS-BK

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	222
Length L (Imperial)	6.1
Length L (Metric)	155.0
Fixation Method	Omega Clip
Identification Plate Position	none
Tie Closure	plastic pawl
Width W (Imperial)	0.19
Width W (Metric)	4.7
Bundle Diameter Min (Imperial)	0.08
Bundle Diameter Min (Metric)	2.0
Bundle Diameter Max (Imperial)	1.38
Bundle Diameter Max (Metric)	35.0
Thickness T (Metric)	1.35

Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Foot Part Material	PA66HIRHS
Material Shortcut	PA66HS PA66HIRHS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.