

## Specification Sheet

Part Number: 156-01555

Friction tab inside the fir tree allows the tie to sit in mount without falling out prior to installation.

Fir tree provides low insertion effort yet demonstrates high extraction resistance.

Disc feature prevents rattling in high-vibration applications and protects against debris ingress.



2-Piece Cable Tie with Fir Tree Mount, 5.9"L, 0.22 - 0.25" Mounting Hole, 100lb, PAEK, Beige, 500/bg

Article Number 156-01555

Type PAT100RFT6LG

Color Beige (BGE)

Quantity Per pack

Product Description HellermannTyton's fir tree mounts provide a secure grip in a mounting hole. The mount can slide along the cable tie to adjust orientation as needed. Fir tree mounts are designed to provide a low insertion force and high extraction force. This mount is sold as an assembly with the cable tie.

Short Description 2-Piece Cable Tie with Fir Tree Mount, 5.9"L, 0.22 - 0.25" Mounting Hole, 100lb, PAEK, Beige, 500/bg

Global Part Name PAT100RFT6LG-PAEK-BGE

Minimum Tensile Strength (Imperial) 100

Minimum Tensile Strength (Metric) 445

Length L (Imperial) 5.9

Length L (Metric) 149.9

Fixation Method Fir tree for round holes

Identification Plate Position none

Tie Closure plastic pawl

Width W (Imperial) 0.33

Width W (Metric) 8.0

Bundle Diameter Min (Imperial) 0.06

Bundle Diameter Min (Metric) 1.5

Bundle Diameter Max (Imperial) 1.38

Bundle Diameter Max (Metric) 35.0

Height H (Imperial) 0.75

Height H (Metric) 19.20

Panel Thickness Min (Imperial)	0.05
Panel Thickness Max (Imperial)	0.24
Panel Thickness Min (Metric)	1.25
Panel Thickness Max (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.22 - 0.25 "
Mounting Hole Diameter D (Metric)	5.6 - 6.4 mm
Mounting Hole Diameter D Min (Imperial)	0.22
Mounting Hole Diameter D Max (Imperial)	0.25
Mounting Hole Diameter D Max (Metric)	6.4
Disc Diameter (Metric)	18.6
Disc Diameter (Imperial)	0.73

Material Polyaryletherketone (PAEK)

Foot Part Material PAEK

Material Shortcut PAEK

Flammability UL 94 V-0

Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-67°F to +392°F (-55°C to +200°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)