

Specification Sheet

Part Number: 156-02723



One-piece ratchet closure allows for easy installation during pre- or final assembly.

Easy release feature simplifies quick adjustments and maintenance.

Impact modified, heat and UV stabilized PA66 provides long-term durability, indoors and out.

3M™ VHB™ adhesive on base creates an incredible bond with mounting surface.

Adhesive Mount Ratchet Clamp, 0.50 - 0.77" Bundle Dia, MB5A, PA66HIRHSUV, Black, 25/bg

Article Number	156-02723
----------------	-----------

Type	IRCBMB5A
------	----------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	The Adhesive Mount Ratchet Clamp offers versatility when managing wires, cables and hoses. Ultra-strong adhesive base attaches where holes don't exist or are undesirable, so no additional hardware is needed for securing to a or panel. The robust design and durable materials make it ideal for heavy duty applications, both indoors and out. The adjustable clamp can be closed by hand to the desired diameter. The release feature allows easy and nondestructive removal of cables simply by using a flat-head screwdriver. In this way, the clamp can be reused or serviced without removing it from the mounting surface.
Short Description	Adhesive Mount Ratchet Clamp, 0.50 - 0.77" Bundle Dia, MB5A, PA66HIRHSUV, Black, 25/bg
Global Part Name	IRCBMB5A-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	100
Minimum Tensile Strength (Metric)	445
Length L (Imperial)	1.37
Length L (Metric)	34.8
Fixation Method	Adhesive
Width W (Imperial)	1.37
Width W (Metric)	34.9
Bundle Diameter Min (Imperial)	0.5
Bundle Diameter Min (Metric)	12.70
Bundle Diameter Max (Imperial)	0.77

Bundle Diameter Max (Metric)	19.56
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Adhesive	Acrylic
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)