

Specification Sheet

Part Number: 156-03014

Three-piece wide strap tie and coupler assembly bundles and separates two routings at any angle from parallel to 90 degrees from each other.

Wide strap ties minimize pinching of soft hoses and convoluted tubing, while the coupler protects routings from friction and abrasion.

Space-saving coupler means more room for routings.



3-Piece Wide Strap Tie with Coupler, 15.1" Long, 0.37" - 4.12" Dia, 120lbs, PA66HIRHSUV, Black, 100/bg

Article Number 156-03014

Type DUALWSRASSY

Color Black (BK)

Quantity Per pack

Product Description Couplers simplify connecting two cable ties for routing and separating bundles. Designed to allow up to 90 degrees of rotation, these assemblies are ideal for applications in which the bundle, pipe or hose requires slight movement in relation to the fastening point.

Short Description 3-Piece Wide Strap Tie with Coupler, 15.1" Long, 0.37" - 4.12" Dia, 120lbs, PA66HIRHSUV, Black, 100/bg

Global Part Name DUALWSRASSY-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)	120
Minimum Tensile Strength (Metric)	535
Length L (Imperial)	15.1
Length L (Metric)	383.0
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.5
Width W (Metric)	12.7
Bundle Diameter Min (Imperial)	0.59
Bundle Diameter Min (Metric)	15.0
Bundle Diameter Max (Imperial)	3.86
Bundle Diameter Max (Metric)	98.0
Height H (Imperial)	0.43
Height H (Metric)	10.86

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)