

Specification Sheet

Part Number: 157-00224

All-in-one bundling and fastening solution reduces costs and assembly time.

Anti-rotational oval fastener forces bundle to travel in intended direction.

Offset cable ties route and position bundles away from a mounting hole to protect them from rubbing, heat or obstructions.



1-Piece Cable Tie with Oval Fir Tree Mount with Disc, 8.5"L, 6.2 x 12.2 mm;6.5 x 12.5 mm;6.5 x 13.0 mm or 7.0 x 12.0 mm Mounting Hole, PA66HIRHSUV, Black, 500/bg

Article Number 157-00224

Type T50ROSFTOVAL12.5A

Color Black (BK)

Quantity Per pack

Product Description One-piece offset cable tie and mount offers a simple bundling and mounting solution. The innovative design of this fir tree establishes a 360-degree interface with the panel hole, ensuring a more secure fit. The oval shape won't rotate once inserted, ensuring proper routing of wires and hoses. Offset feature positions bundles away from a mounting hole. The disc feature prevents rattling in high-vibration applications and protects against debris ingress.

Short Description	1-Piece Cable Tie with Oval Fir Tree Mount with Disc, 8.5"L, 6.2 x 12.2 mm;6.5 x 12.5 mm;6.5 x 13.0 mm or 7.0 x 12.0 mm Mounting Hole, PA66HIRHSUV, Black, 500/bg
Global Part Name	T50ROSFTOVAL12.5A-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	222.4
Length L (Imperial)	8.5
Length L (Metric)	215.9
Offset Length (Imperial)	0.49
Offset Length (Metric)	12.5
Fixation Method	Fir Tree for oval holes
Identification Plate Position	none
Releasable Closure	No
Variant	Outside Serrated
Width W (Imperial)	0.18
Width W (Metric)	4.70
Bundle Diameter Min (Imperial)	0.08

Bundle Diameter Min (Metric)	2.0
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Thickness T (Imperial)	0.05
Thickness T (Metric)	1.35
Height H (Imperial)	0.52
Height H (Metric)	13.15
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.27
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.75
Mounting Hole Diameter D (Imperial)	0.26 x 0.49 " 0.26 x 0.51 " 0.24 x 0.48 " 0.28 x 0.47 "
Mounting Hole Diameter D (Metric)	6.5 x 12.5 mm 6.5 x 13.0 mm 7.0 x 12.0 mm 6.2 x 12.2 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.51
Mounting Hole Diameter D Max (Metric)	7.0
Disc Diameter (Metric)	17.63 x 23.63

Disc Diameter (Imperial)	0.69 x 0.93
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)