

Specification Sheet

Part Number: 157-00268



- One-piece bundling and fastening solution reduces costs and assembly time.
- Low-profile fir tree avoids obstructions on the opposite side of the panel.
- HellermannTyton's 4x oval prevents bundle rotation while providing best-in-class installation ergonomics and extraction resistance for four common oval sizes.
- The fir tree branch design on all four sides makes a 360-degree interface with the panel, creating a more secure fit into the hole.
- Disc feature prevents rattling in high-vibration applications and protects against debris ingress.

1-Piece Cable Tie with Oval Fir Tree with Disc, 8.5"L, 6.2 x 12.2 mm;6.5 x 12.5 mm;6.5 x 13.0 mm or 7.0 x 12.0 mm Hole Dia, PA66HIRHSUV, Bk, 1000/bg

Article Number	157-00268
Type	T50ROSFTSOVAL
Color	Black (BK)
Quantity Per	pack
Product Description	One-piece cable tie and mount offers a simple bundling and mounting solution. The innovative design of this fir tree establishes a 360-degree interface with the panel hole, ensuring a more secure fit. The oval shape won't rotate once inserted, ensuring proper routing of wires and hoses. The disc feature prevents rattling in high-vibration applications and protects against debris ingress.

Short Description	1-Piece Cable Tie with Oval Fir Tree with Disc, 8.5"L, 6.2 x 12.2 mm;6.5 x 12.5 mm;6.5 x 13.0 mm or 7.0 x 12.0 mm Hole Dia, PA66HIRHSUV, Bk, 1000/bg
Global Part Name	T50ROSFTSOVAL-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	8.5
Length L (Metric)	215.9
Fixation Method	Fir tree for round holes
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Outside Serrated
Width W (Imperial)	0.18
Width W (Metric)	4.70
Bundle Diameter Min (Imperial)	0.08
Bundle Diameter Min (Metric)	2.0

Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Height H (Imperial)	0.32
Height H (Metric)	8.05
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.12
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	3.0
Mounting Hole Diameter D (Imperial)	0.28 x 0.47 " 0.26 x 0.49 " 0.26 x 0.51 " 0.24 x 0.48 "
Mounting Hole Diameter D (Metric)	6.2 x 12.2 mm 6.5 x 13.0 mm 7.0 x 12.0 mm 6.5 x 12.5 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.51
Mounting Hole Diameter D Max (Metric)	7.0
Disc Diameter (Metric)	17.6 x 23.6
Disc Diameter (Imperial)	0.69 x 0.93

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com