

Specification Sheet

Part Number: DCT110HIRK2



Provides dual separation between bundles to prevent chafing and abrasion.

150lb. tensile strength ensures enough strength for heavy duty applications.

Straps are releasable for increased serviceability.

Dual Clamp Tie, 19.20" Long, 0.25" Stud Dia, 2.30" Max Bundle Dia, 150lb, PA66HIRHSUV, Black, 50/pkg

Article Number 115-31100

Type DCT11

Color Black (BK)

Quantity Per pack

Product Description Dual-Clamp Ties are designed to provide parallel separation between hoses, wires, cables, and tubing to protect them from abrasion. These ties have an optional mounting hole for securing bundles along the chassis of trucks, trailers, and heavy duty equipment. The unique one-piece design features the dual head centered on the strap.

Short Description Dual Clamp Tie, 19.20" Long, 0.25" Stud Dia, 2.30" Max Bundle Dia, 150lb, PA66HIRHSUV, Black, 50/pkg

Global Part Name DCT11-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)	150
Minimum Tensile Strength (Metric)	667
Length L (Imperial)	19.2
Length L (Metric)	487.68
Fixation Method	Weld Stud Fixing
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.5
Width W (Metric)	12.7
Bundle Diameter Min (Imperial)	0.25
Bundle Diameter Min (Metric)	6.4
Bundle Diameter Max (Imperial)	2.28
Bundle Diameter Max (Metric)	58.0
Thickness T (Imperial)	0.06

Thickness T (Metric)	1.4
Height H (Imperial)	0.8
Height H (Metric)	20.32
Mounting Hole Diameter D (Imperial)	0.20 "
Mounting Hole Diameter D (Metric)	6.2 mm
Mounting Hole Diameter D Min (Imperial)	0.20
Mounting Hole Diameter D Max (Imperial)	0.20
Mounting Hole Diameter D Max (Metric)	6.2
Stud Diameter (Metric)	M6
Stud Diameter (Imperial)	1/4
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 50

Package Quantity (Metric) 50

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)