

## Specification Sheet

Part Number: HDM190HIRC2



Mount and tie combination makes it easy to service bundles in the field.

Made from impact modified, heat stabilized, UV resistant material, ideal for heavy duty environments.

Eliminates the needs for multiple sized fix diameter clamps.

Article Number 151-00134

Type HDM19

Color Black (BK)

Quantity Per pack

Product Description These mounts contain a small tab inside the mounting hole to temporarily engage the threads, which allows assemblers to preinstall the mount on a stud before securing with a washer and a nut. For use with HellermannTyton heavy duty T120, T250, T255 and Wide Strap Cable Ties.

Short Description Standard Torque Cable Tie Mount, Mtg Hole Dia. 0.1875", Max Torque 115.0 in lbs, PA66HIRHSUV, Black, 100/pkg

Global Part Name HDM19-PA66HIRHSUV-BK

Length L (Imperial)	1.43
Length L (Metric)	36.3
Fixation Method	Screw Mounting and Rivet
Width W (Imperial)	0.76
Width W (Metric)	19.3
Height H (Imperial)	0.66
Height H (Metric)	16.7
Cable Tie Width Max (Imperial)	0.50
Cable Tie Width Max (Metric)	12.7
Mounting Hole Diameter D (Imperial)	0.19 "
Mounting Hole Diameter D (Metric)	4.7 mm
Mounting Hole Diameter D Max (Metric)	4.76
Stud Diameter (Metric)	4.8 mm
Stud Diameter (Imperial)	0.19

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Maximum Torque (kgf-cm)	132.5
Maximum Torque (lbf-ft)	9.583
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.