

Specification Sheet

Part Number: HDM250HIRC2



Mount and tie combination makes it easy to service bundles in the field.

Made from impact modified, heat stabilized, UV resistant material, ideal for heavy duty environments.

Eliminates the needs for multiple sized fix diameter clamps.

Standard Torque Cable Tie Mount, Mtg Hole Dia. 0.25", Max Torque 115.0 in lbs, PA66HIRHSUV, Black, 100/pkg

Article Number	151-00437
----------------	-----------

Type	HDM25
------	-------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	These mounts contain a small tab inside the mounting hole to temporarily engage the threads, which allows assemblers to preinstall the mount on a stud before securing with a washer and a nut. For use with HellermannTyton heavy duty T120, T250, T255 and Wide Strap Cable Ties.
---------------------	---

Short Description	Standard Torque Cable Tie Mount, Mtg Hole Dia. 0.25", Max Torque 115.0 in lbs, PA66HIRHSUV, Black, 100/pkg
-------------------	--

Global Part Name	HDM25-PA66HIRHSUV-BK
------------------	----------------------

Length L (Imperial)	1.41
Length L (Metric)	36.3
Fixation Method	Screw Mounting and Rivet
Width W (Imperial)	0.75
Width W (Metric)	19.3
Height H (Imperial)	0.66
Height H (Metric)	16.7
Cable Tie Width Max (Imperial)	0.5
Cable Tie Width Max (Metric)	12.7
Mounting Hole Diameter D (Imperial)	0.25 "
Mounting Hole Diameter D (Metric)	6.2 mm
Mounting Hole Diameter D Max (Metric)	6.2
Stud Diameter (Metric)	6.2 mm
Stud Diamater (Imperial)	0.25

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Maximum Torque (kgf-cm)	132.5
Maximum Torque (lbf-ft)	9.583
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)