

## Specification Sheet

Part Number: IMP2.510C2

Identification Marker Plates can be marked with a permanent pen, printed labels or hot stamped for a wide variety of labeling options.

Any size bundle diameter can be marked because it is only dependent upon the length of the cable tie selected, provided the cable tie width does not exceed .29".

The marker plates are stamped from nylon, making them a durable and long term method of identification.

The mounting holes are positioned to allow the marker to be mounted as a flag, tag or wrapped around the cable or bundle for a wide variety of installed positions.



Article Number 151-42259

Type IMP2.5

Color White (WH)

Quantity Per pack

Product Description Identification Marker Plates can be mounted in any direction, either vertically or horizontally as flags, tags, or wraparound identification plates. They can be hot stamped or marked with HellermannTyton marking pens (T82-S), thermal transfer labels, or laser labels. The markers are manufactured from nylon and are white in color.

|                                |   |
|--------------------------------|---|
| Short Description              | Identification Marker Plate, 2.5" x .75", Nylon, White, 100/pkg |
| Global Part Name               | IMP2.5-PA66-WH  |
| Length L (Imperial)            | 2.5   |
| Length L (Metric)              | 63.5  |
| Fixation Method                | Others  |
| Identification Plate Position  | attached to bundle  |
| Variant                        | Other   |
| Width W (Imperial)             | 2.5   |
| Width W (Metric)               | 19.3  |
| Thickness T (Imperial)         | 0.016   |
| Thickness T (Metric)           | 0.4   |
| Height H (Imperial)            | 0.75  |
| Height H (Metric)              | 19.05   |
| Cable Tie Width Max (Imperial) | 0.18  |
| Cable Tie Width Max (Metric)   | 4.80  |

|                              |                                  |
|------------------------------|----------------------------------|
| Material                     | Polyamide 6.6 (PA66)             |
| Material Shortcut            | PA66                             |
| Flammability                 | UL 94 V-2                        |
| Halogen Free                 | Yes                              |
| UV Resistant (Yes/No)        | No                               |
| Operating Temperature        | -40°F to +185°F (-40°C to +85°C) |
| Reach Compliant (Article 33) | Yes                              |
| ROHS Compliant               | Yes                              |
| Package Quantity (Imperial)  | 100                              |
| Package Quantity (Metric)    | 100                              |
| Customs Number               | 3926909988                       |
| Weight (Metric)              | 0.06                             |
| Weight (Imperial)            | 0.132                            |

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)