

## Specification Sheet

Part Number: IT50R0M4



Identification plate feature allows bundles to be easily marked and identified.

Wire and cable harnesses can be secured and identified using just one product, which saves time.

Plates can be marked manually with a permanent marker or with a pre-printed adhesive label.

Identification Tie, 8" Long, 50lb Tensile Strength, PA66, Black, 1000/pkg

Article Number 111-85013

Type IT50R

Color Black (BK)

Quantity Per pack

Product Description Identification Cable Ties feature an identification plate that allows wire and cable bundles to be easily marked and identified. These ties enable wire and cables to be secured and identified using just one product, saving installation time. The plates can be marked using a permanent marker or with a HellermannTyton adhesive label.

Short Description Identification Tie, 8" Long, 50lb Tensile Strength, PA66, Black, 1000/pkg

Global Part Name IT50R-PA66-BK

|                                     |                    |
|-------------------------------------|--------------------|
| Minimum Tensile Strength (Imperial) | 50                 |
| Minimum Tensile Strength (Metric)   | 225                |
| Length L (Imperial)                 | 8.0                |
| Length L (Metric)                   | 203.2              |
| Fixation Method                     | None               |
| Identification Plate Position       | attached to bundle |
| Releasable Closure                  | No                 |
| Tie Closure                         | plastic pawl       |
| Variant                             | Inside Serrated    |
| Width W (Imperial)                  | 1.1                |
| Width W (Metric)                    | 28.0               |
| Bundle Diameter Min (Imperial)      | 0.37               |
| Bundle Diameter Min (Metric)        | 9.5                |
| Bundle Diameter Max (Imperial)      | 1.75               |
| Bundle Diameter Max (Metric)        | 44.5               |
| Height H (Imperial)                 | 0.51               |

|                                 |                                  |
|---------------------------------|----------------------------------|
| Height H (Metric)               | 12.9                             |
| Outside Diameter Max (Imperial) | 1.73                             |
| Outside Diameter Min (Metric)   | 9.50                             |
| Outside Diameter Min (Imperial) | 0.37                             |
| Outside Diameter Max (Metric)   | 44.50                            |
| Material                        | Polyamide 6.6 (PA66)             |
| Material Shortcut               | PA66                             |
| Flammability                    | UL 94 V-2                        |
| Halogen Free                    | Yes                              |
| UV Resistant (Yes/No)           | No                               |
| Use Conditions                  | For Indoor and Outdoor Use       |
| Operating Temperature           | -40°F to +185°F (-40°C to +85°C) |
| Reach Compliant (Article 33)    | Yes                              |
| ROHS Compliant                  | Yes                              |
| Certification/Specification     | UL                               |

UL Recognized (US) Yes

UL Recognized (US and Canada) Yes

Package Quantity (Imperial) 1000

Package Quantity (Metric) 1000

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)