

## Specification Sheet

Part Number: MSMP5/109C2



Mounting plates allow multiple bundles to run parallel.

The mounts are secured using two screws, while the bundles are attached using cable ties in any of the available slots.

Article Number 151-25519

Type MSMP5/10

Color Natural (NA)

Quantity Per pack

Product Description HellermannTyton mounting plates allow multiple cable to be run in parallel. The mount is secured with two screws and the cables are attached to the plate by using a cable tie through any of the available slots.

Short Description Cable Tie Mounting Plate, 8.05 x .62", 0.2" Hole Dia, 0.3" Max Tie Width, PA66, Natural, 100/pkg

Global Part Name MSMP5/10-PA66-NA

Length L (Imperial)	8.05
Length L (Metric)	204.47
Fixation Method	Screw Mount
Width W (Imperial)	0.62
Width W (Metric)	15.8
Cable Ties	T18 - T120
Height H (Imperial)	0.21
Height H (Metric)	5.30
Cable Tie Width Max (Imperial)	0.3
Cable Tie Width Max (Metric)	7.6
Mounting Hole Diameter D (Imperial)	0.2 "
Mounting Hole Diameter D (Metric)	5.1 mm
Mounting Hole Diameter D Max (Metric)	5.1
Mounting Hole Centers (Imperial)	1.5
Material	Polyamide 6.6 (PA66)

Material Shortcut	PA66
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL   ANSI/UL 62275 UL   ANSI/UL 1565 UL   ANSI/UL 746B
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)