

Specification Sheet

Part Number: T120L0HSK2



Heat stabilized heavy-duty cable ties provide excellent resistance to high heat exposures.

Head design provides high tensile strength with very low insertion force.

Heavy Duty Cable Tie, 30" Long, UL Rated, 120lb Tensile Strength, PA66HS, Black, 50/pkg

Article Number	111-12450
Type	T120L
Color	Black (BK)
Quantity Per	pack
Product Description	Heavy duty T-Series cable ties feature inside serrations to provide a positive hold on wire and cable bundles. Durable head design guarantees high tensile strength and a low insertion force. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Heavy Duty Cable Tie, 30" Long, UL Rated, 120lb Tensile Strength, PA66HS, Black, 50/pkg
Global Part Name	T120L-PA66HS-BK

Minimum Tensile Strength (Imperial)	120
Minimum Tensile Strength (Metric)	535
Length L (Imperial)	30.0
Length L (Metric)	760.0
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.30
Width W (Metric)	7.6
Bundle Diameter Min (Imperial)	0.2
Bundle Diameter Min (Metric)	5.0
Bundle Diameter Max (Imperial)	8.86
Bundle Diameter Max (Metric)	225.0
Thickness T (Metric)	1.9
Cable Tie Head Length (Imperial)	0.39

Cable Tie Head Width (Imperial)	0.51
Height H (Metric)	7.8
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Plenum Rating	AH-2
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL 62275
UL Recognized (US)	Yes
UL Listed (US and Canada)	Yes

UL Recognized (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)