

## Specification Sheet

Part Number: T150XLL4X2



Engineered and manufactured for maximum performance and quality

Made from 100% high-quality plastic to ensure efficient recycling

Inside serration for a strong grip onto bundles

Easy application either manually or with a processing tool

Heavy Duty Cable Tie, 52" Long, UL Rated, 175lb Tensile Strength, PA66, Yellow, 25/pkg

Article Number 111-15302

Type T150XLL

Color Yellow (YE)

Quantity Per pack

Product Description HellermannTyton heavy duty cable ties offer a higher tensile strength for heavy load applications. The head design guarantees high tensile strength, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Heavy Duty Cable Tie, 52" Long, UL Rated, 175lb Tensile Strength, PA66, Yellow, 25/pkg

Global Part Name T150XLL-PA66-YE

Minimum Tensile Strength (Imperial)	175
Minimum Tensile Strength (Metric)	780
Length L (Imperial)	52.0
Length L (Metric)	1325.0
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.35
Width W (Metric)	8.9
Bundle Diameter Min (Imperial)	5.98
Bundle Diameter Min (Metric)	152.0
Bundle Diameter Max (Imperial)	15.94
Bundle Diameter Max (Metric)	405.0
Material	Polyamide 6.6 (PA66)

Material Shortcut	PA66
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL   ANSI/UL 746B UL   ANSI/UL 62275 UL   ANSI/UL 1565
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)