

## Specification Sheet

Part Number: T30MR0M4

Screw mount style creates low insertion and high extraction force.

Choose from several tensile strengths and lengths to accommodate a range of applications.



1-Piece Cable Tie with Screw Mount, 6.3" Long, #8 Screw, 1.3" Max Bundle Dia, 30lb, PA66, Black, 1000/pkg

Article Number 113-03011

Type T30MR

Color Black (BK)

Quantity Per pack

Product Description One-piece Screw Mount Cable Ties fasten with a screw or bolt to provide secure routing of cable bundles. Multiple configurations are available to cover a range of bundle sizes and tensile strengths.

Short Description 1-Piece Cable Tie with Screw Mount, 6.3" Long, #8 Screw, 1.3" Max Bundle Dia, 30lb, PA66, Black, 1000/pkg

Global Part Name T30MR-PA66-BK

|                                     |                 |
|-------------------------------------|-----------------|
| Minimum Tensile Strength (Imperial) | 30              |
| Minimum Tensile Strength (Metric)   | 135             |
| Length L (Imperial)                 | 6.3             |
| Length L (Metric)                   | 160.0           |
| Fixation Method                     | Screw Mount     |
| Identification Plate Position       | none            |
| Releasable Closure                  | No              |
| Tie Closure                         | plastic pawl    |
| Variant                             | Inside Serrated |
| Width W (Imperial)                  | 0.14            |
| Width W (Metric)                    | 3.5             |
| Bundle Diameter Min (Imperial)      | 0.06            |
| Bundle Diameter Min (Metric)        | 1.5             |
| Bundle Diameter Max (Imperial)      | 1.26            |
| Bundle Diameter Max (Metric)        | 32.0            |
| Thickness T (Imperial)              | 0.05            |

|                                       |                                  |
|---------------------------------------|----------------------------------|
| Thickness T (Metric)                  | 1.2                              |
| Height H (Imperial)                   | .17                              |
| Height H (Metric)                     | 4.20                             |
| Mounting Hole Diameter D (Imperial)   | 0.17 "                           |
| Mounting Hole Diameter D (Metric)     | 4.3 mm                           |
| Mounting Hole Diameter D Max (Metric) | 4.3                              |
| Material                              | Polyamide 6.6 (PA66)             |
| Material Shortcut                     | PA66                             |
| Flammability                          | UL 94 V-2                        |
| UV Resistant (Yes/No)                 | No                               |
| Use Conditions                        | For Indoor and Outdoor Use       |
| Plenum Rating                         | AH-2                             |
| Operating Temperature                 | -40°F to +185°F (-40°C to +85°C) |
| Reach Compliant (Article 33)          | Yes                              |
| ROHS Compliant                        | Yes                              |

|                               |            |
|-------------------------------|------------|
| Certification/Specification   | UL 62275   |
| UL Recognized (US)            | Yes        |
| UL Listed (US and Canada)     | Yes        |
| UL Recognized (US and Canada) | Yes        |
| UL Listed (US)                | Yes        |
| Package Quantity (Imperial)   | 1000       |
| Package Quantity (Metric)     | 1000       |
| Customs Number                | 3926909988 |

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)