

Specification Sheet

Part Number: T30R0UVC2

UV stabilized cable ties contain an inhibitor which prolongs the life of the tie in UV exposures.

Inside serrations allow for strong grip on cables and wire bundles.

Head design provides high tensile strength with very low insertion force.

Bent tail ensures a quick and simple installation.



UV Resistant Cable Tie, 6" Long, UL Rated, 30lb Tensile Strength, PA66UV, Black, 100/pkg

Article Number 112-03060

Type T30R

Color Black (BK)

Quantity Per pack

Product Description Used in the solar industry and other applications, HellermannTyton offers cable ties made of UV stabilized PA66UV material. This material provides additional protection against UV radiation for long-term outdoor use and is available in various styles, tensile strengths, and bundle diameters. T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description	UV Resistant Cable Tie, 6" Long, UL Rated, 30lb Tensile Strength, PA66UV, Black, 100/pkg
Global Part Name	T30R-PA66UV-BK
Minimum Tensile Strength (Imperial)	30
Minimum Tensile Strength (Metric)	135
Length L (Imperial)	5.83
Length L (Metric)	148.0
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.14
Width W (Metric)	3.6
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.5
Bundle Diameter Max (Imperial)	1.38
Bundle Diameter Max (Metric)	35.0

Thickness T (Imperial)	0.05
Thickness T (Metric)	1.2
Material	Polyamide 6.6 UV-resistant (PA66UV)
Material Shortcut	PA66UV
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	VG 95387 Part 4 CAGE Code 53421
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	100

Package Quantity (Metric) 100

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)