

Specification Sheet

Part Number: T30RSF0M4

All-in-one bundling and fastening solution reduces costs and assembly time.

The arrowhead design of these ties offers a low insertion force and a high extraction force.

High-spec materials and superior design deliver versatility, performance and value.



1-Piece Cable Tie with Arrowhead Mount, 6.3"L, 30lb, 0.04 - 0.09" Panel Thickness, PA66HS, Black, 1000/pkg

Article Number 126-00702

Type T30RSF(U)

Color Black (BK)

Quantity Per pack

Product Description One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. The arrowhead design of this push mount inserts easily and locks securely in place. HellermannTyton's one-piece mounting ties combine high-specification materials with superior design to deliver dependable performance in a range of applications.

Short Description 1-Piece Cable Tie with Arrowhead Mount, 6.3"L, 30lb, 0.04 - 0.09" Panel Thickness, PA66HS, Black, 1000/pkg

Global Part Name T30RSF(U)-PA66HS-BK

Minimum Tensile Strength (Imperial) 30

Minimum Tensile Strength (Metric) 135

Length L (Imperial) 6.3

Length L (Metric) 160.02

Fixation Method Arrowhead

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.14

Width W (Metric) 3.6

Bundle Diameter Min (Imperial) 0.06

Bundle Diameter Min (Metric) 1.6

Bundle Diameter Max (Imperial) 1.22

Bundle Diameter Max (Metric) 31.0

Thickness T (Imperial)	0.05
Thickness T (Metric)	1.2
Height H (Imperial)	.20
Height H (Metric)	5.70
Panel Thickness Min (Imperial)	0.04
Panel Thickness Max (Imperial)	0.09
Panel Thickness Min (Metric)	0.9
Panel Thickness Max (Metric)	2.4
Mounting Hole Diameter D (Imperial)	0.19 - 0.22 "
Mounting Hole Diameter D (Metric)	4.7 - 5.6 mm
Mounting Hole Diameter D Min (Imperial)	0.19
Mounting Hole Diameter D Max (Imperial)	0.22
Mounting Hole Diameter D Max (Metric)	5.6

Material Polyamide 6.6 heat stabilized (PA66HS)

Material Shortcut PA66HS

Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL-ZODZ2.E64139
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)