

Specification Sheet

Part Number: T50R0HSUVM4

Heat and UV stabilized cable ties provide excellent resistance to high heat and UV exposures

Head design contains clamping rails to provide full circumferential compression around bundles

Bent tail allows for quick insertion into head



High-Temp Cable Tie, 8" Long, UL Rated, 50lb Tensile Strength, PA66HSUV, Black, 1000/pkg

Article Number 111-04907

Type T50R

Color Black (BK)

Quantity Per pack

Product Description HellermannTyton standard cable ties feature inside serrations providing a positive hold onto wire and cable bundles. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description High-Temp Cable Tie, 8" Long, UL Rated, 50lb Tensile Strength, PA66HSUV, Black, 1000/pkg

Global Part Name T50R-PA66HSUV-BK

Minimum Tensile Strength (Imperial) 50

Minimum Tensile Strength (Metric) 225

Length L (Imperial) 7.95

Length L (Metric) 202.0

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.18

Width W (Metric) 4.6

Bundle Diameter Min (Imperial) 0.06

Bundle Diameter Min (Metric) 1.5

Bundle Diameter Max (Imperial) 1.97

Bundle Diameter Max (Metric) 50.0

Thickness T (Imperial) 0.05

Thickness T (Metric)	1.2
Cable Tie Head Length (Imperial)	0.29
Cable Tie Head Width (Imperial)	0.3
Material	Polyamide 6.6 heat and UV stabilized (PA66HSUV)
Material Shortcut	PA66HSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000

Customs Number

3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)