

[Home](#) / [Build Your Own Indicator](#) / [Conxrite Panel Mount Indicator](#) / [5mm](#) / [CNX 310 Series](#) / [LMH 5mm 0.281"D Cable Assembly 0.5W 6"L](#)

LMH 5mm 0.281"D Cable Assembly 0.5W 6"L

SKU: CNX_310_012_X_2_1_06

Category: [CNX 310 Series](#)

Description

Stock Availability

Technical Downloads

Product Description

The CNX 310 series cable assemblies make quick and easy plug-in connections between panel mounted LEDs with lenses and a power source. Options include a broad selection of LEDs, choices of wire size, length and color, and a variety of wire terminations. With an integrated resistor, the CNX 310 series can be used on circuits from 3 to 28 volts. Panel thickness can vary from 1/32" to 1/4". The CNX 310 series is connected to the panel when coupled with a VCC press-fit lens.

Additional Information

Mounting Hole Dimension

Dia. 0.281"

LED Size

5mm (T-1 3/4)

Length Wire Leads

6.0"

Wire Gauge

22 AWG

RoHS

Yes

REACH Compliant

Yes

Conflict Mineral Free

Yes

Resistor

120 ohm

Wire Colors *White Black*

Plating

—

Style

—

LMH Angle

—

Connector
with/with out wire

Connector plus resistor & wire

Pin Configuration

—

LMH Termination
Wire

—

Termination

Wirelead Ends Stripped

Number of Circuits

—

Position

One Position

VCC CONTACT CAREERS WARRANTY POLICY TERMS & CONDITIONS PRIVACY & SECURITY STATEMENT



© 2015, 2016, 2017, 2018 Visual Communications
Company, LLC
Contact Sales 1.800.522.5546



© 2015, 2016, 2017, 2018 Visual Communications Company, LLC

We use cookies to ensure that we give you the best experience on our website. Your continued use of the site constitutes your acceptance of this policy.

Ok