



Color: ■ silver-colored

Similar to illustration

Technical data

Marking method	Thermal transfer
Marking	plain
Delivery form	Roll
Delivery form configuration	500 markers/reel; 1 line
Printing device	Smart Printer (thermal transfer printer)

Physical data

Depth	0.09 mm
Marking surface	25 x 50 mm

Mechanical data

Mounting type	Sticking
Smear resistance	in conjunction with 258-5005 Ink Ribbon

Material data

Color	silver-colored
Material	Polyester
UV resistance	EN 60068-2-5:2010 Procedure B
Adhesive information	Acrylic; permanent
Halogen-free	Yes
Weight	300 g
Fire load	0 MJ

Environmental requirements

Ambient temperature (storage)	≤+21 °C
Ambient temperature (operation)	-40 ... +150 °C
Relative humidity	40 ... 50 %

Commercial data

eCl@ss 10.0	27-40-06-29
eCl@ss 9.0	27-40-06-29
ETIM 8.0	EC001288
ETIM 7.0	EC001288
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4055143389037
Customs tariff number	39199080888

Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product
Compliance 210-812



Documentation

Operating Instructions

210-804 Information on
handling print material 1
28.08.2020 pdf
1347,39 KB



1 Compatible Products

1.1 Optional Accessories

1.1.1 Marking

1.1.1.1 Marking device



Item No.: 258-5000

Thermal transfer printer; Smart Printer; for
complete control cabinet marking; 300
dpi; With marking material