

<https://www.wago.com/211-504>



Color:  white

Similar to illustration

### Technical data

Suitable	for wire cross-section 10 ... 16 mm <sup>2</sup>
Marking method	Thermal transfer
Delivery form	Roll
Delivery form configuration	15 m/roll
Printing device	Smart Printer (thermal transfer printer)

### Physical data

Depth	0.185 mm
-------	----------

### Mechanical Data

Mounting type	Sliding on
Shrink rate	2:1
Smear resistance	in conjunction with 258-5005 Ink Ribbon

### Material Data

Color	white
Material	Polyolefin
UV resistance	EN 60068-2-5:2010 Procedure B
Adhesive information	without adhesive
Halogen-free	Yes
Weight	328.3 g
Fire load	0 MJ

**Environmental requirements**

Surrounding air temperature (storage)	+10 ... +25 °C
Ambient temperature (operation)	-55 ... +125 °C
Relative humidity	45 ... 55 %

**Commercial data**

eCl@ss 10.0	27-40-04-01
eCl@ss 9.0	27-40-04-01
ETIM 8.0	EC001530
ETIM 7.0	EC001530
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DK
GTIN	4055143370295
Customs tariff number	85472000900