
Item no.: 231-136/001-000
Product description: HEADER; STRAIGHT SOLDER PIN, 1X1 MM / 0.039X 0.039 IN; 6 POLE; PIN SPACING 5 MM / 0.197 IN; MATING DIRECTION PERPENDICULAR TO PCB; WITH CLOSED END



Packing unit 100 4*25 pieces

Pin spacing from	5 mm
Pin spacing from	0.197 in
pole count	6
Voltage CSA	300 V
Voltage UL	300 V
Current rating UL	10 A
Current rating CSA	10 A
Measured voltage EN	250 V
Measured shock voltage	4 kV
Pollution degree	3
Current intensity EN	12 A
Weight	2.064 g
Color	gray
Height	12 mm
Height	0.472 in
Width	33.2 mm
Width	1.307 in
Depth	8.4 mm
Depth	0.331 in



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
231-136/001-000	BV	11915/A0	400	16	2,5
231-136/001-000	CSA	154112-1466354	300	10	1x1
231-136/001-000	DEMKO	88126	250	16	2,5
231-136/001-000	KEMA	98.2486.01	250	12	
231-136/001-000	KR	HMB05880-EL003	250/400	12/16	2,5
231-136/001-000	UL	E45171	600	10	1x1
231-136/001-000	UL	E45172	300	10	1x1
231-136/001-000	VDE	5675ÜGBI.2	250	12	

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected