



Color: ■ black

Similar to illustration

### Connection data

Number of levels	1	<b>Connection 1</b>	
		Pole number	10

### Physical data

Pin spacing	3.5 mm / 0.138 inches
Solder pin length	3.5 mm
Solder pin diameter	1 mm
Drilled hole diameter with tolerance	1.2 (+0.05) mm

### Mechanical data

Suitable	Pin spacing: 3.5 mm / 0.138 inch
----------	----------------------------------

### Plug-in connection

Contact type (pluggable connector)	Male connector/plug
Connector (connection type)	for PCB
Mating direction to the PCB	90 °

### PCB contact

PCB contact	THT
-------------	-----

### Material data

Note (material data)	<a href="#">Information on material specifications can be found here</a>
Color	black
Insulation material	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0 MJ
Weight	1 g

### Commercial data

Product Group	4 (Printed Circuit Connectors)
eCl@ss 10.0	27-14-11-92
eCl@ss 9.0	27-14-11-92
ETIM 8.0	EC002848
ETIM 7.0	EC002848
PU (SPU)	500 pcs
Packaging type	Box
Country of origin	DE
GTIN	4044918506830
Customs tariff number	85369010000

### Downloads

#### Environmental Product Compliance

Compliance Search			
Environmental Product Compliance 252-910			

### Documentation

Additional Information			
Technical Section	03.04.2019	pdf 1949.09 KB	

### CAD/CAE-Data

CAD data			
2D/3D Models 252-910			