

Item no.:	257-844
Product description:	MODULAR PCB TERMINAL BLOCK; 2 SOLDER PINS / POLE; 1 POLE; PIN SPACING 5/5.08 MM / 0.2 IN; ANGLED LEVER; FRONT-/SIDE-ENTRY



Packing unit 500 5*100 pieces

Pin spacing from	5 mm
Pin spacing up to	5,08 mm
Pin spacing from	0,197 in
Pin spacing up to	0,2 in
pole count	1
Cross section from [mm ²]	0,08 mm ²
Cross section to [mm ²]	2,5 mm ²
Cross section from [AWG]	28 AWG
Cross section to [AWG]	12 AWG
Connection method	CAGE CLAMP®CONNECTION
Voltage UL	300 V
Current UL	15 A
Measured voltage EN	250 V
Measured shock voltage	4 kV
Pollution degree	3
Current intensity EN	16 A
Measured voltage EN	500 V
Measured shock voltage	4 kV
Pollution degree	2
Current intensity EN	16 A
Weight	1,143 g
Color	blue
Wiring type	Front-/Side-entry
No. of connection Points	1
No. of potentials	1
Height	20,2 mm
Height	0,795 in
Width	5 mm
Width	0,197 in
Depth	14,2 mm
Depth	0,559 in
Strip length from	5 mm
Strip length to	6 mm
Strip length	0,22 in

	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
257-844	BBJ	B/12/697/03	250	16	0,5-2,5
257-844	BV	11915/A0	500/250	16	0,08-2,5

257-844	CCA	DK2082	250	16	0,5-2,5
257-844	CSM	017956	250/500	16	0,08-2,5
257-844	DEMKO	98-04355	500	16	0,5-2,5
257-844	DNV	E6998	500/250	16	0,08-2,5
257-844	GL	17296-00HH	500/250	16	0,5-2,5
257-844	RMR	99.00007.250	250	16	0,5-2,5
257-844	RosTesT	B09523	250/500	16	0,08-2,5
257-844	UL	E45172	300	15	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected