
Item no.: 281-101
Product description: 2-CONDUCTOR THROUGH TERMINAL BLOCK; LATERAL MARKING; for DIN 35 rail; SIDE-ENTRY; CAGE CLAMP®CONNECTION; HORIZONTAL TYPE



Packing unit 100 pieces

Product group	1 (Rail Mounted Terminal Blocks)
Cross section from [mm²]	0,08 mm²
Cross section to [mm²]	4 mm²
Cross section from [AWG]	28 AWG
Cross section to [AWG]	12 AWG
Connection method	CAGE CLAMP®CONNECTION
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	32 A
Weight	5,934 g
Color	grey
Wiring type	Side-entry
No. of connection Points	2
No. of potentials	1
Height	32,5 mm
Height	1,28 in
Width	6 mm
Width	0,236 in
Depth	42,5 mm
Depth	1,67 in
Strip length from	9 mm
Strip length to	10 mm
Strip length	0,37 in

Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm²]
281-101	ABS	05-HG476175/1-PDA	800	32	4,0
281-101	BBJ	B/12/700/03	800	32	4,0
281-101	BV	07436/Co	800	32	4,0
281-101	CCA	NL5591/1	800		4
281-101	CSA	154112-1505034	600	25	28-12
281-101	DEMKO	75942	750		4
281-101	Dep.MaE	CS4866N	600	25	4
281-101	DNV	E7570	800	32	4,0
281-101	GL	17295-00HH	800	32	4
281-101	KEMA	2076376.01	800	32	4
281-101	KR	HMB05880-EL001	500/800	10/35	4
281-101	LR	91/20112(E5)	800	32	4,0
281-101	NEMKO	M52727/01	750		4
281-101	PRS	TE/1718/880590/08	800		4
281-101	PTB	PTB98Atex3110U	550	28	4
281-101	RMR	11130002	800	32	4,0
281-101	SABS	ED751/8189	750		4
281-101	SABS-EX	e741/85712/W491	550	24	
281-101	UL	E45172	600	20	28-12
281-101	UR	E45172	600	20	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected