

Item no.: 281-684
 Product description: 3-CONDUCTOR THROUGH TERMINAL BLOCK; CENTRE MARKING; SUITABLE FOR EX I APPLICATIONS; for DIN 35 rail; FRONT-ENTRY; CAGE CLAMP®CONNECTION



Packing unit 50 pieces

Product group	1 (Rail Mounted Terminal Blocks)
Cross section from [mm ²]	0,08 mm ²
Cross section to [mm ²]	4 mm ²
Cross section from [AWG]	28 AWG
Cross section to [AWG]	12 AWG
Connection method	CAGE CLAMP®CONNECTION
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	32 A
Weight	11,003 g
Color	blue
Wiring type	Front-entry
No. of connection Points	3
No. of potentials	1
Height	29 mm
Height	1,14 in
Width	6 mm
Width	0,236 in
Depth	73,5 mm
Depth	2,89 in
Strip length from	9 mm
Strip length to	10 mm
Strip length	0,37 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
281-684	ABS	05-HG476175/1-PDA	800	32	4,0
281-684	BBJ	B/12/700/03	800	32	4,0
281-684	BV	07436/C0			0,08-4
281-684	CCA	NL5591/1	800	32	4
281-684	CSA	154112-1505034	600	25	28-12
281-684	DEMKO	75942	750		4
281-684	Dep.MaE	CS4866N	600	25	4
281-684	DNV	E7570	800	32	4,0
281-684	GL	17295-00HH	800	32	4
281-684	KEMA	2076376.01	800	32	4
281-684	KR	HMB05880-EL001	500/800	10/35	4
281-684	LR	91/20112(E5)	800	32	4,0
281-684	PRS	TE/1718/880590/08	800	32	4
281-684	RMR	11130002	800	32	4,0
281-684	UR	E45172	600	20	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected