

## Data Sheet | Item Number: 711-140

Transformer terminal block; 10-pole; CAGE CLAMP® connection for conductors;  
4,00 mm²; gray

<https://www.wago.com/711-140>



Color: ■ gray

Similar to illustration

### Electrical data

#### Ratings per IEC/EN

Ratings per	IEC/EN 60664-1
Rated voltage (III/2)	800 V
Rated impulse voltage (III/2)	8 kV
Rated current	25 A
Legend (ratings)	(III / 2) Δ Overvoltage category III / Pollution degree 2

### Connection data

Connection points	10
Total number of potentials	10
Number of connection types	1

#### Connection 1

Connection technology	CAGE CLAMP®
Strip length	9 ... 10 mm / 0.35 ... 0.39 inches
Pole number	10

### Physical data

Width	75 mm / 2.953 inches
Height	35 mm / 1.378 inches
Depth	23.5 mm / 0.925 inches

### Material Data

Note (material data)	<a href="#">Information on material specifications can be found here</a>
Color	gray
Fire load	0.681 MJ
Weight	33.1 g

## Commercial data

eCl@ss 10.0	27-14-11-10
eCl@ss 9.0	27-14-11-10
ETIM 8.0	EC000398
ETIM 7.0	EC000398
PU (SPU)	15 pcs
Packaging type	Box
Country of origin	DE
GTIN	4044918819510
Customs tariff number	85369010000

## Approvals / Certificates

### General approvals



Approval	Standard	Certificate Name
CCA DEKRA Certification B.V.	EN 60998	NTR NL-7194
CCA DEKRA Certification B.V.	EN 60998	2160584.54
CSA DEKRA Certification B.V.	C22.2 No. 158	1101145
UL UL International Germany GmbH	UL 1059	E45172

## Downloads

### Environmental Product Compliance

#### Compliance Search

Environmental Product  
Compliance 711-140



## Documentation

### Additional Information

Technical Section  
03.04.2019  
pdf  
1949.09 KB



## CAD/CAE-Data



CAD data

2D/3D Models 711-140



CAE data

EPLAN Data Portal  
711-140



ZUKEN Portal 711-140

