

Data Sheet | Item Number: 206-1125

Wire stripper "Quickstrip Vario"; Standard, 0.03 mm² ... 16 mm²; with wire cutter

<https://www.wago.com/206-1125>



Color: green/black

Connection data

Strip length	3 ... 21 mm / 0.12 ... 0.83 inches
Solid conductor	0.03 ... 16 mm ² / 32 ... 5 AWG
Fine-stranded conductor	0.03 ... 16 mm ² / 32 ... 5 AWG
Stranded conductor	0.03 ... 16 mm ² / 32 ... 5 AWG

Mechanical data

Blade, replaceable	Yes
Cutting function	Yes
Conductor cross-section setting, automatic	Yes
Partial stripping function	Yes

Material data

Color	green/black
Fire load	0 MJ
Weight	195 g
Conductor material	for copper; for aluminum

Commercial data

PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4055143885478
Customs tariff number	8203200000

Product classification	
UNSPSC	27112116
ETIM 9.0	EC002109
ETIM 8.0	EC002109
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Downloads

Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 206-1125	↓

Documentation

Operating Instructions		
Bedienungsanleitung 206-1125 Quickstrip Vario 2023	pdf 926.95 KB	↓
Operating instructions 206-1125 Quickstrip Vario EN	pdf 925.13 KB	↓

1 Compatible Products

1.1 Optional Accessories

1.1.1 Tool

1.1.1.1 Stripping tool



[Item No.: 206-1128](#)
Blade set; Oval blade, 10 mm² ... 16 mm²; for 206-1125



[Item No.: 206-1126](#)
Blade set; Standard, 0.03 mm² ... 16 mm²; for 206-1125



[Item No.: 206-1127](#)
Blade set; V-blade, 0.14 mm² ... 4 mm²; for 206-1125



[Item No.: 206-1131](#)
Spare cut protector; for 206-1125



[Item No.: 206-1132](#)
Spare gripping jaws; for 206-1125



[Item No.: 206-1129](#)
Spare strip length stop; for 206-1125

Installation Notes



Cutting a conductor.



Partially stripping a conductor.