

Data Sheet | Item Number: 282-387

End and separator plate; 1.5 mm thick; with lock-out seal option; orange

<https://www.wago.com/282-387>



Color: ■ orange

Physical data

Width	1.5 mm / 0.059 inches
Height	122 mm / 4.803 inches
Depth	71.7 mm / 2.823 inches

Material data

Note (material data)	Information on material specifications can be found here
Color	orange
Material group	I
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.408 MJ
Weight	9.6 g

Environmental requirements

Processing temperature	-35 ... +85 °C
Continuous operating temperature	-60 ... +105 °C

Commercial data

Product Group	1 (Rail Mounted Terminal Blocks)
PU (SPU)	50 (10) pcs
Packaging type	Box
Country of origin	DE
GTIN	4017332264907
Customs tariff number	85389099990

Product Classification	
UNSPSC	39121702
eCl@ss 10.0	27-14-11-33
eCl@ss 9.0	27-14-11-33
ETIM 9.0	EC000886
ETIM 8.0	EC000886
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Downloads

Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 282-387	↓

Documentation

Bid Text			
282-387	19.02.2019	xml 2.65 KB	↓
282-387	03.03.2017	doc 23.50 KB	↓

CAD/CAE-Data

CAD data	
2D/3D Models 282-387	↓

CAE data	
EPLAN Data Portal 282-387	↓
WSCAD Universe 282-387	↓
ZUKEN Portal 282-387	↓

Installation Notes



A lock-out seal can be used on the disconnect link in notched "I" position.

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: www.wago.com