

Features:

- 7/8" screw connection: Industry-proven connection technology for a large selection of different conductors
- High protection class for safe field applications
- Vibration- and shock-resistant via integrated locking mechanism
- PUR coating

Technical data

Operating data

Operating voltage	600 VAC/VDC
Operating current	9 A

Safety and protection

Rated impulse withstand voltage	4 kV
Protection type	IP67

Connection data

Connection 1

Connection technology	7/8"; 3-pole; angled socket
-----------------------	-----------------------------

Material data

Fire load	0 MJ
Weight	49.3 g

Environmental requirements

Ambient temperature (operation)	-25 ... +80 °C
---------------------------------	----------------

Commercial data

PU (SPU)	1 pcs
Packaging type	Bag
Country of origin	DE
GTIN	4055143726924
Customs tariff number	85366990990

Product Classification

UNSPSC	39121413
ETIM 9.0	EC002635
ETIM 8.0	EC002635
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Downloads

Environmental Product Compliance







Compliance Search

Environmental Product
Compliance
787-6716/9400-000



Documentation

Bid Text

787-6716/9400-0000	19.02.2019	xml 3.40 KB	
787-6716/9400-000	12.06.2019	docx 16.66 KB	
787-6716/9400-000	12.06.2019	pdf 65.18 KB	
787-6716/9400-0000	12.06.2019	doc 29.50 KB	
787-6716/9400-0000	12.06.2019	docx 16.63 KB	
787-6716/9400-0000	12.06.2019	pdf 65.22 KB	

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: www.wago.com