

Item no.: 255-743
 Product description: MODULAR PCB TERMINAL BLOCK 2 SOLDER PINS / POLE
 1 POLE PIN SPACING 5/5.08 MM / 0.2 IN WITH PUSH
 BOTTOMS



Produkt kann von Bild abweichen / product may differ

Packing unit 500 5*100 pieces

RoHS compliant

Product group	4 (Printed Circuit)
Weight	1.153 g
Color	light gray
No. of connection Points	1
No. of potentials	1
pole count	1
Height	14.2 mm
Height	0.559 in
Width	5 mm
Width	0.197 in
Depth	18.3 mm
Depth	0.72 in
Pin spacing from	5 mm
Pin spacing up to	5.08 mm
Pin spacing from	0.197 in
Pin spacing up to	0.2 in
Pollution degree	2
Measured voltage EN	320 V

Measured shock voltage	4 kV
Current intensity EN	24 A
Pollution degree	2
Measured voltage EN	630 V



Measured shock voltage	4 kV
Current intensity EN	24 A
Connection method	CAGE CLAMP® CONNECTION
Cross section [mm ²]	0.08 - 2.5 mm ²
Wiring method	solid
Cross section [mm ²]	0.08 - 2.5 mm ²
Cross section [mm ²]	0.25 - 1.5 mm ²
Cross section [mm ²]	0.25 - 1.5 mm ²
Cross section [AWG]	28 - 12 AWG
Strip length from	5 mm
Strip length to	6 mm
Material group	I



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
255-743	ABS	04-HG469925/1-PDA	500/250	16	0,5-2,5
255-743	BV	11915/A0	500/250	16	0,08-2,5
255-743	CCA	NL6248	250	24	0,08-2,5
255-743	CSA	18677-45	300	15	28-12
255-743	DNV	E-9215	500/250	16	0,08-2,5
255-743	GL	17296-00HH	500/250	16	0,5-2,5
255-743	KEMA	2110204.02	250	10	0,5-2,5
255-743	RMR	11130002	250	16	0,5-2,5
255-743	UR	E45172	300	15	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected