

Item no.: 261-351  
 Product description: 4-CONDUCTOR END TERMINAL BLOCK WITHOUT FIXING FOOT FOR TERMINAL STRIPS WITH FIXING FEET



Packing unit 200 4\*50 pieces

Product group	9 (Std Chassis Mt Blocks)
Cross section [mm <sup>2</sup> ]	0.08- 2.5 mm <sup>2</sup>
Cross section [AWG]	28 - 14 AWG
Connection method	CAGE CLAMP® CONNECTION
Number of strands	2
Measured voltage EN	500 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	24 A
Weight	3.62 g
Color	gray
Wiring type	Sideentry
No. of connection Points	4
No. of potentials	1
Height	18 mm
Height	0.709 in
Width	10 mm
Width	0.394 in
Depth	28 mm
Depth	1.103 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in
Customs Tariff No.	85369010
Country of Origin	Schweiz