

CableLine
CLI C 1-3 GE/SW 9 MP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

Type	CLI C 1-3 GE/SW 9 MP
Order No.	0252611529
Version	CableLine, Conductor and cable markers, 2.5 - 5 mm, 3 x 4.2 mm, yellow
GTIN (EAN)	4008 190124267
Qty.	200 pc(s).

Creation date August 17, 2020 8:36:42 PM CEST

Catalogue status 14.08.2020 / We reserve the right to make technical changes.

CableLine
CLI C 1-3 GE/SW 9 MP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	4.2 mm	Width (inches)	0.165 inch
Height	3 mm	Height (inches)	0.118 inch
Depth	5 mm	Depth (inches)	0.197 inch
Net weight	0.055 g		

General data

Colour	yellow	Colour of printing	black
Halogen	Yes	Insulation cross-section, max.	5 mm
Material	PVC, soft, without Cadmium	Material colour according to resistance code	4
Operating temperature range	-30...80 °C	Orientation of print	horizontal
Printed characters	Numbers	Printing	9
Printing method	hot-embossing	Recommended industries	Process, Machinery
Type of printing	Standard	UL 94 flammability rating	V-0
Version	MultiPack	Width	4.2 mm

Conductor and cable markers

Conductor O.D.	2.5 - 5 mm	Conductor O.D., max.	5 mm
Conductor O.D., min.	2.5 mm	Conductor cross-section, max.	4 mm ²
Conductor cross-section, min.	1.5 mm ²	Halogen	Yes

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
eClass 9.0	27-40-04-01	eClass 9.1	27-40-04-01
eClass 10.0	27-40-04-01	UNSPSC	44-12-17-08

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Product Change Notification	PCN CableLine_DE PCN CableLine_EN

Data sheet

**CableLine
CLI C 1-3 GE/SW 9 MP**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings



Similar to illustration